

Product data sheet

Characteristics

2032VRJA5-WE

SOCKET OUTLET 2G RJ45 CAT 5



Main

| | |
|------------------|------------------|
| Range of product | Series 2000 |
| Colour | White electric |
| Product brand | Clipsal |
| Quantity per set | Set of 2 |
| Cover type | Full cover plate |




Complementary

| | |
|------------------|-------------------------|
| Colour code | WE |
| Marking | Without marking |
| Local signalling | Without light indicator |

Packing Units

| | |
|------------------------------|--------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 79 g |
| Package 1 Height | 35 mm |
| Package 1 width | 75 mm |
| Package 1 Length | 115 mm |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 5 |
| Package 2 Weight | 0.4 kg |
| Package 2 Height | 119 mm |
| Package 2 width | 83 mm |
| Package 2 Length | 179 mm |
| Unit Type of Package 3 | CAR |
| Number of Units in Package 3 | 100 |
| Package 3 Weight | 8 kg |
| Package 3 Height | 305 mm |
| Package 3 width | 296 mm |
| Package 3 Length | 436 mm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation |  REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Compliant  EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information |  Yes |

China RoHS Regulation

 [China RoHS Declaration](#)

Environmental Disclosure

 [Product Environmental Profile](#)
