

Product data sheet

Characteristics

2033A-WE

SWITCH 3 GANG ARCHITRAVE 10A 250V



Main

Range of product	Series 2000
Product brand	Clipsal
Device presentation	Basic element with full cover plate and grid

Complementary

Switch function	1-pole
Actuator	Rocker
Number of rocker	3
Number of poles	1
Device mounting	Flush
Fixing mode	By screws
Material	PC (polycarbonate)
Surface finish	Glossy
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	74 g
Package 1 Height	25 mm
Package 1 width	35 mm
Package 1 Length	140 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	0.816 kg
Package 2 Height	95 mm
Package 2 width	138 mm
Package 2 Length	239 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Weight	8.56 kg
Package 3 Height	254 mm
Package 3 width	348 mm
Package 3 Length	445 mm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile