

Product data sheet

Characteristics

2034A-WE

SWITCH 4 GANG ARCHITRAVE 10A 250V



Main

| | |
|---------------------|--|
| Range of product | Series 2000 |
| Product brand | Clipsal |
| Device presentation | Basic element with full cover plate and grid |

Complementary

| | |
|--------------------------------|--------------------|
| Switch function | 1-pole |
| Actuator | Rocker |
| Number of rocker | 4 |
| Number of poles | 1 |
| Device mounting | Flush |
| Fixing mode | By screws |
| Material | PC (polycarbonate) |
| Local signalling | without |
| [Ue] rated operational voltage | 250 V AC |
| Rated current | 10 A |
| Marking | Without marking |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 85 g |
| Package 1 Height | 25 mm |
| Package 1 width | 35 mm |
| Package 1 Length | 141 mm |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Weight | 0.94 kg |
| Package 2 Height | 95 mm |
| Package 2 width | 138 mm |
| Package 2 Length | 239 mm |
| Unit Type of Package 3 | CAR |
| Number of Units in Package 3 | 100 |
| Package 3 Weight | 9.6 kg |
| Package 3 Height | 254 mm |
| Package 3 width | 348 mm |
| Package 3 Length | 445 mm |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |