

Product data sheet

Characteristics

2034HA-WE

Flush Switch, 2000 Series, 4 Gang, 250VAC, 10A, Standard, Horizontal



Main

Range of product	Series 2000
Product brand	Clipsal
Assembly Type	Basic element with full cover plate and grid

Complementary

Number of poles	1
Installation Type	Flush
Number Of Switches	4
Material	PC (polycarbonate)
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking
Mounting Type	By screws
Actuator	Rocker
Switch function	1-pole

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24 mm
Package 1 Width	116 mm
Package 1 Length	76 mm
Package 1 Weight	0.11 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	12.2 cm
Package 2 Width	14.1 cm
Package 2 Length	16.1 cm
Package 2 Weight	1.1 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	25.4 cm
Package 3 Width	34.8 cm
Package 3 Length	44.5 cm
Package 3 Weight	11.0 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations