

# Product data sheet

## Characteristics

# 2036VA-WE

## SWITCH 6 GANG VERTICAL 10A 250V



### Main

Range of product	Series 2000
Product brand	Clipsal
Device presentation	Basic element with full cover plate and grid

### Complementary

Switch function	2-way 1-way
Number of rocker	6
Device mounting	Flush
Fixing mode	By screws
Material	PC (polycarbonate)
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	10 A
Marking	Without marking
Actuator	Rocker

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.136 kg
Package 1 Height	24 mm
Package 1 width	76 mm
Package 1 Length	116 mm
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	1.48 kg
Package 2 Height	122 mm
Package 2 width	141 mm
Package 2 Length	161 mm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	7.5 kg
Package 3 Height	157 mm
Package 3 width	305 mm
Package 3 Length	445 mm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>