

Product data sheet

Characteristics

2036VKT4X-WE

2000 Series, Keytag Type Switches Suit 4 x
20A Circuits - with extra Switch



Main

Range of product	Series 2000
Product brand	Clipsal
Device presentation	Basic element with full cover plate



Complementary

Switch function	2-way
Local signalling	without
[Ue] rated operational voltage	250 V AC
Rated current	20 A
Marking	Without marking
Actuator	Key

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	7.6 cm
Package 1 Length	11.6 cm
Package 1 Weight	0.16 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	9.5 cm
Package 2 Width	13.8 cm
Package 2 Length	23.9 cm
Package 2 Weight	905 g
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	25.4 cm
Package 3 Width	34.8 cm
Package 3 Length	44.5 cm
Package 3 Weight	9.2 kg

Offer Sustainability

RECh Regulation	 RECh Declaration
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	 China RoHS Declaration