

## Product data sheet

### Characteristics

# 21507

## Acti9 - comb busbar - 3L+N balanced - 9 mm pitch - 24 modules - 80A



### Main

Range	Acti 9
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Lines description	3L + N
Length in 18 mm modules	24

### Complementary

Number of ways	24 ways N + 3 L (balanced)
Poles configuration for 1 way	1 x 3P + N 1 x 3P 3 x 1P + N
Connection pitch	9 mm
Connector type	Tooth
Distance between way	54 mm
Marking	N L1 N L2 N L3
Insulation	Insulated
Device presentation	Cuttable
[Ie] rated operational current	80 A at 40 °C
[Ue] rated operational voltage	230 V AC Ph/N 400 V AC Ph/Ph
[Ui] rated insulation voltage	440 V AC conforming to IEC 61439-1
[Uimp] rated impulse withstand voltage	6 kV
Mounting mode	Horizontal
Mounting location	Top on tunnel type terminals
9 mm pitches	48
Width	432 mm
Colour	Light grey (RAL 7035)
Range compatibility	Acti 9 iDPN Acti9 iDPN Vigi Multi 9 N40 Vigi N40 Vigi Multi 9 N40

### Environment

Standards	EN/IEC 60439-1 IEC 60947-7
Fire resistance	960 °C ( 30 s ) conforming to IEC 60695-2-1
Pollution degree	3 conforming to IEC 60947-7

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	268 g
Package 1 Height	3 cm
Package 1 width	3.2 cm
Package 1 Length	48.5 cm
Unit Type of Package 2	P12
Number of Units in Package 2	448
Package 2 Weight	136.936 kg
Package 2 Height	112 cm
Package 2 width	80 cm
Package 2 Length	120 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	8
Package 3 Weight	2.242 kg
Package 3 Height	52 cm
Package 3 width	7 cm
Package 3 Length	11 cm

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	18 months
----------	-----------