

Product data sheet

Characteristics

221/32-EO

Solid Fittings, PVC, Conduit Locating Flanges, 32mm



Main

Colour	Electric orange
Product brand	Clipsal
Range of product	Series 221

Complementary

Colour code	EO
Material	Plastic
External diameter	90 mm
Height	40 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4 cm
Package 1 Width	9 cm
Package 1 Length	9 cm
Package 1 Weight	52.2 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.2 cm
Package 2 Width	16.4 cm
Package 2 Length	21.8 cm
Package 2 Weight	610 g
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	21 cm
Package 3 Width	34.8 cm
Package 3 Length	44.5 cm
Package 3 Weight	6.6 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile