

Product data sheet

Characteristics

23-WE

SWITCHED SOCKET TWIN LARGE 10A 250V



Main

Range of product	Standard Series
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric

Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Switch Rocker
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Horizontal
Material	Plastic
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	15 mm
Length	145 mm
Width	86 mm
Fixing center	120 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133:approval number S/1
-----------	---

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	136.0 g
Package 1 Height	1.5 cm
Package 1 width	8.6 cm
Package 1 Length	14.5 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	100
Package 2 Weight	15.5 kg

Package 2 Height	15.7 cm
Package 2 width	30.5 cm
Package 2 Length	44.5 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	5
Package 3 Weight	775.0 g
Package 3 Height	8.4 cm
Package 3 width	12.65 cm
Package 3 Length	17 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile