

## Product data sheet

### Characteristics

# 230DRAS2MI

Clipsal Resi MAX, Meter Box South Australia  
24 Modules With meter isolator MCB 63 A 1P 6  
kA



### Main

Range of product	Resi MAX
Product type	Meter box
Enclosure type	Plain door enclosure
Device application	Distribution Metering
Targeted country	Australia
Targeted region	South Australia

### Complementary

Enclosure mounting	Surface Semi flush
Number of modules	24
Provided equipment	Fascia plate Meter isolator Removable meter panel Enclosure DIN rail Earth and neutral grid assembly
Function available	Clips lead retainer
Protection device type	Miniature circuit breaker (MCB) - 63 A - 1P - 6 kA
Cable entry	Knock-out top and bottom
Type of door	Ventilated removable door with door retainer
Door opening side	Right
Material	Iron (galvanised)
Surface finish	Epoxy powder coat
Width	500 mm
Height	800 mm
Depth	256 mm
Colour	Beige

### Environment

IP degree of protection	IP23
Standards	AS/NZS 3000

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	80.0 cm
Package 1 Width	50.0 cm
Package 1 Length	25.6 cm
Package 1 Weight	20.8 kg

Offer Sustainability

EU RoHS Directive	Under investigation
Circularity Profile	No need of specific recycling operations