

Product data sheet

Characteristics

230DRAS3

Resimax Meterbox 30 module switchboard -
H600 x W610 x D256 mm



Main

Range of product	Resi MAX
Product type	Meter box
Enclosure type	Plain door enclosure
Device application	Metering Distribution
Targeted country	Australia
Targeted region	South Australia

Complementary

Enclosure mounting	Semi flush Surface
Number of modules	30
Provided equipment	Enclosure DIN rail Earth and neutral grid assembly Fascia plate Removable meter panel
Function available	Clips lead retainer
Protection device type	Miniature circuit breaker (MCB) - 63 A - 1P - 6 kA
Cable entry	Knock-out top and bottom
Type of door	Ventilated removable door with door retainer
Door opening side	Right
Lock type	Padlockable
Material	Iron (galvanised)
Surface finish	Epoxy powder coat
Width	610 mm
Height	600 mm
Depth	256 mm
Colour	Beige

Environment

IP degree of protection	IP23
Standards	AS/NZS 3000

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	17.32 kg
Package 1 Height	60 cm
Package 1 width	61 cm
Package 1 Length	25.6 cm

