

Product data sheet

Characteristics

230DRAVL

Resi MAX Meterbox 21 module with service fuse lock - H680 x W470 x D280 mm



Main

| | |
|--------------------|--------------------------|
| Range of product | Resi MAX |
| Product type | Meter box |
| Enclosure type | Plain door enclosure |
| Device application | Distribution Metering |
| Targeted country | Australia |
| Targeted region | Victoria |

Complementary

| | |
|------------------------|--|
| Enclosure mounting | Surface Semi flush |
| Number of modules | 21 |
| Provided equipment | Fuse links Neutral link Removable meter panel Enclosure DIN rail Fascia plate |
| Function available | Fuse protection lock Cable protection slide |
| Protection device type | Miniature circuit breaker (MCB) - 63 A - 1P - 6 kA |
| Cable entry | Knock-out top and bottom Knock-out rear |
| Type of door | Ventilated removable door with door retainer |
| Door opening side | Right |
| Lock type | Padlockable |
| Material | Iron (galvanised) |
| Surface finish | Epoxy powder coat |
| Width | 470 mm |
| Height | 680 mm |
| Depth | 280 mm |
| Colour | Beige |

Environment

| | |
|-------------------------|-------------|
| IP degree of protection | IP23 |
| Standards | AS/NZS 3000 |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 18000 g |
| Package 1 Height | 695 mm |
| Package 1 width | 295 mm |
| Package 1 Length | 485 mm |

Offer Sustainability

| | |
|-------------------|--|
| EU RoHS Directive | Not applicable, out of EU RoHS legal scope |
|-------------------|--|