

## Product data sheet

### Characteristics

# 230DRAVL

## Clipsal Resi MAX, Meter Box Victoria 21 Modules With Service Fuse Lock



### Main

Range of product	Resi MAX
Product type	Meter box
Enclosure type	Plain door enclosure
Device application	Distribution Metering
Targeted country	Australia
Targeted region	Victoria

### Complementary

Enclosure mounting	Surface Semi flush
Number of modules	21
Provided equipment	Fuse links Neutral link Removable meter panel Enclosure DIN rail Fascia plate
Function available	Fuse protection lock Cable protection slide
Protection device type	Miniature circuit breaker (MCB) - 63 A - 1P - 6 kA
Cable entry	Knock-out top and bottom Knock-out rear
Type of door	Ventilated removable door with door retainer
Door opening side	Right
Lock type	Padlockable
Material	Iron (galvanised)
Surface finish	Epoxy powder coat
Width	470 mm
Height	680 mm
Depth	280 mm
Colour	Beige

### Environment

IP degree of protection	IP23
Standards	AS/NZS 3000

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	69.5 cm
Package 1 Width	29.5 cm
Package 1 Length	48.5 cm
Package 1 Weight	18000 g
Unit Type of Package 2	PAL
Number of Units in Package 2	24
Package 2 Height	14.5 cm
Package 2 Width	110 cm
Package 2 Length	110 cm
Package 2 Weight	456000 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>