

Product data sheet

Characteristics

230SMT

Clipsal Resi MAX, Meter Box Tasmania 21 Modules



Main

Range of product	Resi MAX
Product type	Meter box
Enclosure type	Plain door enclosure
Device application	Metering Distribution
Targeted country	Australia
Targeted region	Tasmania

Complementary

Enclosure mounting	Semi flush Surface
Number of modules	21
Provided equipment	Earth and neutral grid assembly DIN rail Fascia plate Enclosure
Protection device type	Miniature circuit breaker (MCB) - 63 A - 1P - 6 kA
Cable entry	Knock-out top and bottom Knock-out rear
Type of door	Ventilated removable door with door retainer
Door opening side	Right
Lock type	Cam lockable
Material	Iron (galvanised)
Surface finish	Epoxy powder coat
Width	464 mm
Height	860 mm
Depth	282 mm
Colour	Beige

Environment

IP degree of protection	IP23
Standards	AS/NZS 3000

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	86.0 cm
Package 1 Width	46.4 cm
Package 1 Length	28.2 cm
Package 1 Weight	17.0 kg

Offer Sustainability

EU RoHS Directive	Under investigation
Circularity Profile	No need of specific recycling operations