

Product data sheet

Characteristics

235S20/3/4-GY

Clipsal - Cable Management, Solid Fittings - PVC, Screwed Converters, 20mm to 3/4 inch



Main

Colour	Grey
Product brand	Clipsal
Range of product	Series 235S

Complementary

Colour code	GY
Material	PVC (polyvinyl chloride)
Connector type	Thread connector
Product destination	Diameter: 20 mm tube
Length	33 mm

Environment

Standards	AS/NZS 2053
-----------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	2.5 cm
Package 1 Length	3 cm
Package 1 Weight	0.02 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Circularity Profile	No need of specific recycling operations