

Product data sheet

Characteristics

235S32BSP40-WE

CONVERTER COND SCR 32 /40MM



Main

| | |
|------------------|----------------|
| Colour | White electric |
| Product brand | Clipsal |
| Range of product | Series 235BSP |

Complementary

| | |
|---------------------|--|
| Colour code | WE |
| Material | PVC (polyvinyl chloride) |
| Connector type | Thread connector |
| Product destination | Diameter: 32 mm tube Diameter: 40 mm tube |
| Length | 49 mm |

Environment

| | |
|-----------|-------------|
| Standards | AS/NZS 2053 |
|-----------|-------------|

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 0.032 kg |
| Package 1 Height | 50 mm |
| Package 1 width | 47 mm |
| Package 1 Length | 47 mm |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 10 |
| Package 2 Weight | 0.37 kg |
| Package 2 Height | 10.6 cm |
| Package 2 width | 10.2 cm |
| Package 2 Length | 14 cm |
| Unit Type of Package 3 | CAR |
| Number of Units in Package 3 | 100 |
| Package 3 Weight | 3.95 kg |
| Package 3 Height | 25 cm |
| Package 3 width | 21.4 cm |
| Package 3 Length | 33.8 cm |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |