

## Product data sheet

### Characteristics

# 236/1S25-GY

Clipsal - Cable Management, Solid Fittings - PVC, Converting Adaptors, 1 Inch Screwed to 25mm Plain



#### Main

Colour	Grey
Product brand	Clipsal

#### Complementary

Colour code	GY
Material	PVC (polyvinyl chloride)
Connector type	Thread connector
Product destination	Diameter: 25 mm tube
Length	40 mm

#### Environment

Standards	AS/NZS 2053
-----------	-------------

#### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.07 cm
Package 1 Width	3.03 cm
Package 1 Length	3.03 cm
Package 1 Weight	11.1 g
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	9.7 cm
Package 2 Width	11.6 cm
Package 2 Length	21.5 cm
Package 2 Weight	0.631 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	500
Package 3 Height	21 cm
Package 3 Width	34.8 cm
Package 3 Length	44.5 cm
Package 3 Weight	6.695 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Circularity Profile	No need of specific recycling operations