

Product data sheet

Characteristics

236/1S25-GY

CONVERT CON ADAPTOR 1in. 25MM



Main

Colour	Grey
Product brand	Clipsal

Complementary

Colour code	GY
Material	PVC (polyvinyl chloride)
Connector type	Thread connector
Product destination	Diameter: 25 mm tube
Length	40 mm

Environment

Standards	AS/NZS 2053
-----------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	11.1 g
Package 1 Height	4.07 cm
Package 1 Width	3.03 cm
Package 1 Length	3.03 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Weight	0.631 kg
Package 2 Height	9.7 cm
Package 2 Width	11.6 cm
Package 2 Length	21.5 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	500
Package 3 Weight	6.695 kg
Package 3 Height	21 cm
Package 3 Width	34.8 cm
Package 3 Length	44.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile