

Product data sheet

Characteristics

236/20S3/4-GY

Clipsal - Cable Management, Solid Fittings - PVC, Converting Adaptors, 20mm Screwed to 3/4 Inch Plain



Main

Colour	Grey
Product brand	Clipsal
Range of product	Series 236

Complementary

Colour code	GY
Material	PVC (polyvinyl chloride)
Connector type	Thread connector
Length	36 mm

Environment

Standards	AS/NZS 2053
-----------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.59 cm
Package 1 Width	2 cm
Package 1 Length	2 cm
Package 1 Weight	7.3 g
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Height	7 cm
Package 2 Width	9.2 cm
Package 2 Length	11.8 cm
Package 2 Weight	0.184 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	400
Package 3 Height	25 cm
Package 3 Width	21.4 cm
Package 3 Length	33.8 cm
Package 3 Weight	3.905 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes