

Product data sheet

Characteristics

236/25S1-GY

Converting Adaptor, Clipsal - Cable Management, PVC, 25mm Screwed to 1 Inch Plain



Main

Colour	Grey
Product brand	Clipsal
Range of product	Series 236

Complementary

Colour code	GY
Material	PVC (polyvinyl chloride)
Connector type	Thread connector
Length	40 mm

Environment

Standards	AS/NZS 2053
-----------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.07 cm
Package 1 Width	3.1 cm
Package 1 Length	3.1 cm
Package 1 Weight	10.8 g
Unit Type of Package 2	BB1
Number of Units in Package 2	50
Package 2 Height	9.7 cm
Package 2 Width	11.6 cm
Package 2 Length	21.5 cm
Package 2 Weight	0.616 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	500
Package 3 Height	21 cm
Package 3 Width	34.8 cm
Package 3 Length	44.5 cm
Package 3 Weight	6.545 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Circularity Profile	No need of specific recycling operations