

Product data sheet

Characteristics

244/16-GY

ELBOW CONDUIT PVC INSP 16MM



Main

Colour	Grey
Product brand	Clipsal
Range of product	Series 244

Complementary

Colour code	GY
Material	PVC (polyvinyl chloride)
Diameter	16 mm
Operating angle	90 °
Length	59 mm

Environment

Standards	AS/NZS 2053
-----------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	5 cm
Package 1 Length	8.5 cm
Package 1 Weight	0.043 kg
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	8.5 cm
Package 2 Width	9.7 cm
Package 2 Length	15 cm
Package 2 Weight	0.5 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	200
Package 3 Height	21 cm
Package 3 Width	34.8 cm
Package 3 Length	44.5 cm
Package 3 Weight	10 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile