

## Product data sheet

### Characteristics

# 244/50-EO

## ELBOW CONDUIT PVC INSP 50MM



### Main

Colour	Electric orange
Product brand	Clipsal
Range of product	Series 244

### Complementary

Colour code	EO
Material	PVC (polyvinyl chloride)
Diameter	50 mm
Operating angle	90 °
Length	119 mm

### Environment

Standards	AS/NZS 2053
-----------	-------------

### Packing Units

Package 1 Weight	0.234 kg
------------------	----------

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.