

Product data sheet

Characteristics

247/16-GY

Solid Fittings, PVC, Solid Elbows, BEnds, 16mm



Main

Colour	Grey
Product brand	Clipsal
Range of product	Series 247

Complementary

Colour code	GY
Material	PVC (polyvinyl chloride)
Diameter	16 mm
Operating angle	90 °
Length	68 mm
Inner radius	41 mm

Environment

Standards	AS/NZS 2053
-----------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2 cm
Package 1 Width	4.5 cm
Package 1 Length	10 cm
Package 1 Weight	13 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	78 cm
Package 2 Width	96 cm
Package 2 Length	120 cm
Package 2 Weight	0.168 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	200
Package 3 Height	258 cm
Package 3 Width	218 cm
Package 3 Length	338 cm
Package 3 Weight	4.2 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile