

Product data sheet

Characteristics

247L32-EO

Clipsal - Cable Management, Conduit Bend, Large Sweep, 90Deg, PVC, 32mm



Main

Colour	Electric orange
Product brand	Clipsal
Range of product	Series 247L

Complementary

Colour code	EO
Material	PVC (polyvinyl chloride)
Diameter	32 mm
Operating angle	90 °
Length	350 mm
Inner radius	312 mm

Environment

Standards	AS/NZS 2053
-----------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.8 cm
Package 1 Width	4.5 cm
Package 1 Length	51.5 cm
Package 1 Weight	216 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	184 cm
Package 2 Width	316 cm
Package 2 Length	474 cm
Package 2 Weight	2.708 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	10
Package 3 Height	184 cm
Package 3 Width	316 cm
Package 3 Length	474 cm
Package 3 Weight	2.708 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes