

Product data sheet

Characteristics

247L40-EO

Clipsal - Cable Management, Conduit Bend,
Large Sweep, 90Deg, PVC, 40mm



Main

Colour	Electric orange
Product brand	Clipsal
Range of product	Series 247L

Complementary

Colour code	EO
Material	PVC (polyvinyl chloride)
Diameter	40 mm
Operating angle	90 °
Length	355 mm
Inner radius	312 mm





Environment

Standards	AS/NZS 2053
-----------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	15.5 cm
Package 1 Length	53.5 cm
Package 1 Weight	342 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	190 cm
Package 2 Width	310 cm
Package 2 Length	462 cm
Package 2 Weight	4.2 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	10
Package 3 Height	190 cm
Package 3 Width	310 cm
Package 3 Length	462 cm
Package 3 Weight	4.2 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations