

## Product data sheet

### Characteristics

# 247LH32-EO

## BEND CONDUIT 45 DEGREE LESS

### ENCLOSURE SWP 32 MM - Electric Orange



#### Main

Colour	Electric orange
Product brand	Clipsal
Range of product	Series 247L

#### Complementary

Colour code	EO
Material	PVC (polyvinyl chloride)
Diameter	32 mm
Operating angle	45 °
Length	270 mm
Inner radius	312 mm

#### Environment

Standards	AS/NZS 2053
-----------	-------------

#### Packing Units

Package 1 Weight	135.800 g
Package 1 Height	37.000 mm
Package 1 width	75.000 mm
Package 1 Length	340.000 mm

#### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>