

## Product data sheet

### Characteristics

# 247LH40-EO

## Conduit Bend, Clipsal - Cable Management, Large Sweep, 45Deg, PVC, 40mm

### Main

Colour	Electric orange
Product brand	Clipsal
Range of product	Series 247L

### Complementary

Colour code	EO
Material	PVC (polyvinyl chloride)
Diameter	40 mm
Operating angle	45 °
Length	280 mm
Inner radius	312 mm





### Environment

Standards	AS/NZS 2053
-----------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	4.5 cm
Package 1 Length	35.0 cm
Package 1 Weight	203.0 g

### Offer Sustainability

Packaging without single use plastic	No
Packaging made with recycled cardboard	No
REACH Regulation	 <a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

---

Circularity Profile	No need of specific recycling operations
Take-back	No

---