

Product data sheet

Characteristics

25-WE

Standard Series, Twin Switch Socket Outlet, 250V, 10A, Standard Size



Main

| | |
|------------------|-----------------|
| Range of product | Standard Series |
| Product brand | Clipsal |

Complementary

| | |
|--------------------------------|-------------------------|
| Control type | ON/OFF button |
| Number of gangs | 2 gangs |
| Pin number | 3 |
| Number of power socket outlets | 2 |
| Actuator | Switch Rocker |
| Fixing mode | By screws |
| Local signalling | Without light indicator |
| Mounting position | Horizontal |
| Material | PC (polycarbonate) |
| Surface finish | Glossy |
| [Ue] rated operational voltage | 250 V AC |
| [In] rated current | 10 A |
| Depth | 16 mm |
| Length | 115 mm |
| Width | 73 mm |
| Fixing center | 84 mm |

Environment

| | |
|-----------|--|
| Standards | AS/NZS 3100 AS/NZS 3112 AS/NZS 3133 AS/NZS 3000:approval number S/1 |
|-----------|--|

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 3 cm |
| Package 1 Width | 7.3 cm |
| Package 1 Length | 11.5 cm |
| Package 1 Weight | 0.101 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |