

## Product data sheet

### Characteristics

# 25/15-WE

## Twin Switch Socket Outlet, Standard Series, 250V, 15A, Standard Size



### Main

Range of product	Standard Series
Product or component type	Switched socket
Product brand	Clipsal

### Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number Of Outlets	2
Actuator	Switch Rocker
Mounting Type	By screws
Local signalling	Without light indicator
Installation Orientation	Horizontal
Material	PC (polycarbonate)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	15 A
Depth	16 mm
Length	115 mm
Width	73 mm
Mounting Centers	84 mm

### Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133 AS/NZS 3000:approval number S/1
-----------	--

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3 cm
Package 1 Width	7.3 cm
Package 1 Length	11.5 cm
Package 1 Weight	0.101 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant with Exemptions
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations