

Product data sheet

Characteristics

25/2V-WE

SWITCHED SOCKET TWIN VERTICAL 10A 250V



Main

Range of product	Standard Series
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric

Complementary

Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Switch Rocker
Fixing mode	By screws
Local signalling	Without light indicator
Mounting position	Vertical
Material	PC (polycarbonate)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	11 mm
Length	115 mm
Width	115 mm
Fixing center	84 x 46 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133 AS/NZS 3000:approval number S/1
-----------	--

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	148.3 g
Package 1 Height	2 cm
Package 1 width	11.6 cm
Package 1 Length	11.5 cm
Unit Type of Package 2	BB1

Number of Units in Package 2	5
Package 2 Weight	740 g
Package 2 Height	12 cm
Package 2 width	13.8 cm
Package 2 Length	15.3 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	8.4 kg
Package 3 Height	25.4 cm
Package 3 width	34.8 cm
Package 3 Length	44.5 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile