

## Product data sheet

### Characteristics

# 258/25-EO

## Solid Fittings, PVC, Plain to Screwed Couplings, Junction Box Entries, 25mm



### Main

Colour	Electric orange
Product brand	Clipsal

### Complementary

Colour code	EO
Material	PVC (polyvinyl chloride)
Connector type	Thread connector
Product destination	Diameter: 25 mm tube

### Environment

Standards	AS/NZS 2053
-----------	-------------

### Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	3.112 cm
Package 1 Length	3.112 cm
Package 1 Weight	10 g
Unit Type of Package 2	Gyári csomagolás
Number of Units in Package 2	20
Package 2 Height	8.5 cm
Package 2 Width	9.7 cm
Package 2 Length	15 cm
Package 2 Weight	0.236 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	1000
Package 3 Height	48.5 cm
Package 3 Width	33.9 cm
Package 3 Length	44.3 cm
Package 3 Weight	12.392 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>