

Product data sheet

Characteristics

25SF-WE

SWITCHED SOCKET TWIN 10A SURGE FILTER



Main

Colour	White electric
Product brand	Clipsal
Range of product	Standard Series

Complementary

Colour code	WE
Control type	ON/OFF button
Number of gangs	2 gangs
Pin number	3
Number of power socket outlets	2
Actuator	Switch Rocker
Mounting position	Horizontal
Fixing mode	By screws
Local signalling	Without light indicator
Material	PC (polycarbonate)
Surface finish	Glossy
[Ue] rated operational voltage	250 V AC
[In] rated current	10 A
Depth	16 mm
Length	115 mm
Width	73 mm
Fixing center	84 mm

Environment

Standards	AS/NZS 3100 AS/NZS 3112 AS/NZS 3133 AS/NZS 3000:approval number S/1
-----------	--

Packing Units

Package 1 Weight	201.000 g
Package 1 Height	62.000 mm
Package 1 width	105.000 mm
Package 1 Length	150.000 mm

Offer Sustainability

EU RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)  [EU RoHS Declaration](#)