

Product data sheet

Characteristics

262P100-EO

Clipsal - Cable Management, Solid Fittings - PVC, Conduit Caps, 100mm - Suits 100mm pressure pipe



Main

Colour	Electric orange
Product brand	Clipsal
Range of product	Series 262

Complementary

Colour code	EO
Material	PVC (polyvinyl chloride)
Diameter	Inner: 114.5 mm Outside: 122 mm
Length	48 mm

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.8 cm
Package 1 Width	12.15 cm
Package 1 Length	12.15 cm
Package 1 Weight	124 g
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Height	14.5 cm
Package 2 Width	17.6 cm
Package 2 Length	19.7 cm
Package 2 Weight	0.732 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Height	42.3 cm
Package 3 Width	34.5 cm
Package 3 Length	45.2 cm
Package 3 Weight	7.862 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes