

Product data sheet

Characteristics

264/4SM-EO

Solid Fittings, PVC, Screwed Reducers, 40mm to 32mm



Main

Colour	Electric orange
Product brand	Clipsal

Complementary

Colour code	EO
Material	PVC (polyvinyl chloride)
Product destination	Diameter: 32 mm tube Diameter: 40 mm tube
Length	29 mm

Environment

Standards	AS/NZS 2053
-----------	-------------

Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	2.8 cm
Package 1 Width	4 cm
Package 1 Length	4 cm
Package 1 Weight	16 g
Unit Type of Package 2	Gyári csomagolás
Number of Units in Package 2	20
Package 2 Height	10.6 cm
Package 2 Width	10.2 cm
Package 2 Length	14 cm
Package 2 Weight	0.372 kg
Unit Type of Package 3	CAR
Number of Units in Package 3	400
Package 3 Height	21 cm
Package 3 Width	34.8 cm
Package 3 Length	44.5 cm
Package 3 Weight	7.83 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile