

Product data sheet

Characteristics

27060

Terminal for aluminium cables, Acti9, from 16 to 50 mm² - set of 1

Main

Range of product	Acti9
Product or component type	Terminal
Accessory / separate part category	Connection accessory

Complementary

[In] rated current	100 A 80 A 63 A 25 A 32 A 40 A 50 A 125 A
Standards	EN/IEC 61439-1
Connections - terminals	Cable connector
Wire stripping length	13 mm
Tightening torque	10 N.m
Range compatibility	Multi9 Multi9 C60 Acti9 Acti9 C60H-DC Acti9 Acti9 iSW Acti9 Acti9 iC60 Acti9 Acti9 Reflex iC60 Acti9 Acti9 iID Acti9 Acti9 iSW-NA Acti9 Acti9 SW60-DC Acti9 Acti9 C60NA-DC Acti9 Acti9 C120NA-DC Multi9 Multi9 ID Acti9 Acti9 DT60 Acti9 Acti9 C120 Acti9 Vigi C120

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.700 cm
Package 1 Width	12.000 cm
Package 1 Length	13.500 cm
Package 1 Weight	20.000 g
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	8.500 cm
Package 2 Width	9.500 cm

Package 2 Length	23.200 cm
Package 2 Weight	306.000 g
Unit Type of Package 3	S03
Number of Units in Package 3	144
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	4.137 kg

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------