

Product data sheet

Characteristics

2727-WE

Clipsal 2000 Series Universal Shaver Socket Outlet 115/240VAC, 22VA



Main

| | |
|---------------------------|------------------|
| Range of product | Series 2000 |
| Product or component type | Socket-outlet |
| Colour | White electric |
| Product brand | Clipsal |
| Quantity per set | Set of 1 |
| Cover type | Full cover plate |

Complementary

| | |
|--------------------------------|-------------------------|
| Colour code | WE |
| Marking | Without marking |
| Local signalling | Without light indicator |
| Device mounting | Flush |
| Fixing mode | By screws |
| Material | Plastic |
| [Ue] rated operational voltage | 115/240 V AC |
| Network frequency | 50 Hz |
| Depth | 57 mm |
| Length | 116 mm |
| Width | 76 mm |
| Fixing center | 84 mm |

Environment

| | |
|-----------|--|
| Standards | AS/NZS 3100 AS/NZS 3112 AS/NZS 3133 AS/NZS 3000:approval number S/1 |
|-----------|--|

Packing Units

| | |
|------------------------------|-----------|
| Unit Type of Package 1 | Db |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 7.0 cm |
| Package 1 Width | 9.1 cm |
| Package 1 Length | 11.7 cm |
| Package 1 Weight | 650.0 g |
| Unit Type of Package 2 | CAR |
| Number of Units in Package 2 | 20 |
| Package 2 Height | 25.0 cm |
| Package 2 Width | 21.4 cm |
| Package 2 Length | 33.8 cm |
| Package 2 Weight | 13.225 kg |

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| REACH Regulation | REACH Declaration |
| EU RoHS Directive | Compliant EU RoHS Declaration |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |