

## Product data sheet

### Characteristics

# 2727RC30-WE

Clipsal 2000 Series RCD Protected Socket Outlet 250V, 20A, Shaver, 30mA RCD



### Main

Range of product	Series 2000
Product or component type	Switched socket
Product brand	Clipsal
Colour	White electric

### Complementary

Control type	ON/OFF button
Number of gangs	1 gang
Pin number	3
Number of power socket outlets	1
Actuator	Switch Rocker
Local signalling	Without light indicator
Mounting position	Horizontal
[Ue] rated operational voltage	250 V AC
[In] rated current	20 A
Depth	57 mm
Length	219 mm
Width	116 mm
Fixing center	84 mm

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	13.8 cm
Package 1 Length	23.9 cm
Package 1 Weight	1080.0 g
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	25.4 cm
Package 2 Width	34.8 cm
Package 2 Length	44.5 cm
Package 2 Weight	11.22 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>