

Product data sheet

Characteristics

279AC12EH-GY

Clipsal - Cable Management, Flexible Electrical
Hose Fittings, Angled Glands (90°), 12mm



Main

Colour	Grey
Product brand	Clipsal
Range of product	Series 279AC
Product or component type	Elbow

Complementary

Colour code	GY
Thread type	M12
Threaded length	1.5 mm
Cable outer diameter	12 mm
Material	PVC (polyvinyl chloride)
Device composition	Lock nut
Operating angle	90 °

Environment

IP degree of protection	IP54
Ambient air temperature for operation	-15...65 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	0.001 kg

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Circularity Profile	No need of specific recycling operations