

Product data sheet

Characteristics

279AC16-GY

Clipsal - Cable Management, Corrugated Fittings, Angled Glands (90°), 16mm



Main

Colour	Grey
Product brand	Clipsal
Range of product	Series 279AC
Product or component type	Elbow

Complementary

Colour code	GY
Thread type	M16
Threaded length	1.5 mm
Cable outer diameter	16 mm
Material	PVC (polyvinyl chloride)
Device composition	Lock nut
Operating angle	90 °

Environment

IP degree of protection	IP54
Ambient air temperature for operation	-15...65 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	3.2 cm
Package 1 Length	5.5 cm
Package 1 Weight	13 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes