

Product data sheet

Characteristics

279AC20-GY

GLAND ANGLED HOSE LOCK NUT



Main

Colour	Grey
Product brand	Clipsal
Range of product	Series 279AC
Product or component type	Elbow

Complementary

Colour code	GY
Thread type	M20
Threaded length	1.5 mm
Cable outer diameter	20 mm
Material	PVC (polyvinyl chloride)
Device composition	Lock nut
Operating angle	90 °

Environment


IP degree of protection	IP54
Ambient air temperature for operation	-15...65 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	24.0 g
Package 1 Height	3.7 cm
Package 1 width	9.5 cm
Package 1 Length	11.4 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	20
Package 2 Weight	0.575 kg
Package 2 Height	8.3 cm
Package 2 width	15.9 cm
Package 2 Length	21 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	400
Package 3 Weight	12.072 kg
Package 3 Height	42.3 cm
Package 3 width	34.5 cm
Package 3 Length	45.2 cm

Offer Sustainability

EU RoHS Directive

Pro-active compliance (Product out of EU RoHS legal scope)  [EU RoHS Declaration](#)

Environmental Disclosure

 [Product Environmental Profile](#)
