

Product data sheet

Characteristics

279AC20HF-BK

GLAND ANGLED HFT LOCK NUT



Main

Colour	Black
Product brand	Clipsal
Range of product	Series 279AC
Product or component type	Elbow

Complementary

Colour code	BK
Thread type	M20
Threaded length	1.5 mm
Cable outer diameter	20 mm
Material	PVC (polyvinyl chloride)
Device composition	Lock nut
Operating angle	90 °

Environment

IP degree of protection	IP54
Ambient air temperature for operation	-15...65 °C

Packing Units

Package 1 Weight	0.060 kg
------------------	----------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile