

## Product data sheet

### Characteristics

# 279AC20HF-BK

## Clipsal - Cable Management, Corrugated Fittings - HFT, Angled Glands (90°), 20mm



### Main

Colour	Black
Product brand	Clipsal
Range of product	Series 279AC
Product or component type	Elbow

### Complementary

Colour code	BK
Thread type	M20
Threaded length	1.5 mm
Cable outer diameter	20 mm
Material	PVC (polyvinyl chloride)
Device composition	Lock nut
Operating angle	90 °

### Environment

IP degree of protection	IP54
Ambient air temperature for operation	-15...65 °C

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.7 cm
Package 1 Width	4.2 cm
Package 1 Length	6.5 cm
Package 1 Weight	22.865 g

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

---

RoHS exemption information

 Yes

---

Circularity Profile

No need of specific recycling operations

---