

## Product data sheet

### Characteristics

# 279AC25HF-BK

## GLAND ANGLED HFT LOCK NUT



### Main

Colour	Black
Product brand	Clipsal
Range of product	Series 279AC
Product or component type	Elbow

### Complementary

Colour code	BK
Thread type	M25
Threaded length	1.5 mm
Cable outer diameter	25 mm
Material	PVC (polyvinyl chloride)
Device composition	Lock nut
Operating angle	90 °

### Environment

IP degree of protection	IP54
Ambient air temperature for operation	-15...65 °C

### Packing Units

Package 1 Weight	0.060 kg
------------------	----------

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>