

Product data sheet

Characteristics

279AC32-GY

GLAND ANGLED HOSE LOCK NUT



Main

Colour	Grey
Product brand	Clipsal
Range of product	Series 279AC
Product or component type	Elbow

Complementary

Colour code	GY
Thread type	M32
Threaded length	1.5 mm
Cable outer diameter	32 mm
Material	PVC (polyvinyl chloride)
Device composition	Lock nut
Operating angle	90 °

Environment

IP degree of protection	IP54
Ambient air temperature for operation	-15...65 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	46.58 g
Package 1 Height	5.7 cm
Package 1 width	4.6 cm
Package 1 Length	10 cm
Unit Type of Package 2	BB1
Number of Units in Package 2	5
Package 2 Weight	0.285 kg
Package 2 Height	10.6 cm
Package 2 width	10.2 cm
Package 2 Length	14 cm
Unit Type of Package 3	CAR
Number of Units in Package 3	50
Package 3 Weight	3.075 kg
Package 3 Height	25 cm
Package 3 width	21.4 cm
Package 3 Length	33.8 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile