

Product data sheet

Characteristics

279AC32HF-BK

Clipsal - Cable Management, Corrugated Fittings - HFT, Angled Glands (90°), 32mm



Main

Colour	Black
Product brand	Clipsal
Range of product	Series 279AC
Product or component type	Elbow

Complementary

Colour code	BK
Thread type	M32
Threaded length	1.5 mm
Cable outer diameter	32 mm
Material	PVC (polyvinyl chloride)
Device composition	Lock nut
Operating angle	90 °

Environment

IP degree of protection	IP54
Ambient air temperature for operation	-15...65 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	46 g

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.