

Product data sheet

Characteristics

279B25-GY

Gland with Bulkhead Flanges, Clipsal - Cable Management, 25mm



Main

Colour	Grey
Product brand	Clipsal
Range of product	Series 279B

Complementary

Colour code	GY
Thread type	M25
Threaded length	1.5 mm
Cable outer diameter	25 mm
Device composition	Without lock nut

Environment

IP degree of protection	IP54
Ambient air temperature for operation	-15...65 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4 cm
Package 1 Width	4.5 cm
Package 1 Length	7.5 cm
Package 1 Weight	25.6 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Circularity Profile	No need of specific recycling operations