

Product data sheet

Characteristics

279B32-GY

FLANGE BULKHEAD ANGLE 32MM



Main

Colour	Grey
Product brand	Clipsal
Range of product	Series 279B

Complementary

Colour code	GY
Thread type	M32
Threaded length	1.5 mm
Cable outer diameter	32 mm
Device composition	Without lock nut

Environment

IP degree of protection	IP54
Ambient air temperature for operation	-15...65 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	38.0 g
Package 1 Height	5.5 cm
Package 1 width	5.5 cm
Package 1 Length	9 cm
Unit Type of Package 2	CAR
Number of Units in Package 2	100
Package 2 Weight	5.66 kg
Package 2 Height	25.4 cm
Package 2 width	34.8 cm
Package 2 Length	44.5 cm
Unit Type of Package 3	BB1
Number of Units in Package 3	5
Package 3 Weight	0.262 kg
Package 3 Height	8.4 cm
Package 3 width	12.65 cm
Package 3 Length	17 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile