

## Product data sheet

### Characteristics

# 279B50-GY

## FLANGE BULKHEAD ANGLE 50MM



### Main

|                  |             |
|------------------|-------------|
| Colour           | Grey        |
| Product brand    | Clipsal     |
| Range of product | Series 279B |

### Complementary

|                      |                  |
|----------------------|------------------|
| Colour code          | GY               |
| Thread type          | M50              |
| Threaded length      | 1.5 mm           |
| Cable outer diameter | 50 mm            |
| Device composition   | Without lock nut |

### Environment

|                                       |             |
|---------------------------------------|-------------|
| IP degree of protection               | IP54        |
| Ambient air temperature for operation | -15...65 °C |

### Packing Units

|                  |          |
|------------------|----------|
| Package 1 Weight | 0.140 kg |
|------------------|----------|

### Offer Sustainability

|                          |  |
|--------------------------|--|
| EU RoHS Directive        | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a> |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>  |

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.