

Product data sheet

Characteristics

279B50-GY

Gland with Bulkhead Flanges, Clipsal - Cable Management, 50mm



Main

Colour	Grey
Product brand	Clipsal
Range of product	Series 279B

Complementary

Colour code	GY
Thread type	M50
Threaded length	1.5 mm
Cable outer diameter	50 mm
Device composition	Without lock nut

Environment

IP degree of protection	IP54
Ambient air temperature for operation	-15...65 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	9 cm
Package 1 Length	12.1 cm
Package 1 Weight	114 g

Offer Sustainability

EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Circularity Profile	No need of specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.