

Product data sheet

Characteristics

279C16-GY

Clipsal - Cable Management, Corrugated Fittings, Straight Glads, 16mm



Main

Colour	Grey
Product brand	Clipsal
Range of product	Series 279C
Tool type	24 mm wrench

Complementary

Colour code	GY
Thread type	M16
Threaded length	1.5 mm
Cable outer diameter	16 mm
Material	PVC (polyvinyl chloride)
Device composition	Lock nut
Installation direction	Straight

Environment

Ambient air temperature for operation	-15...65 °C
---------------------------------------	-------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.9 cm
Package 1 Width	3.6 cm
Package 1 Length	5.3 cm
Package 1 Weight	8 g

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration

RoHS exemption information

 Yes

Circularity Profile

No need of specific recycling operations
